Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4SNLEDLD548SLUNV 4snledld548slunvl840cd1u

Cooper Lighting Solutions

Catalog Number	4SNLEDLD548SLUNV
Manufacturer	Cooper Lighting Solutions
Description	Led Linear Striplight, 120/277 V Ac, 0.125 A @ 277 V, 35 W, Cold Rolled Steel, 4000 K, 80, >60000 H Average Life, Dimmable, 4827 LM Brightness (Lumens), 48 In Length, 1-25/32 In Width, 2-7/8 In Height, 7.2 LB
Weight per unit	5.0 (lbs/each)
Product Category	Led Surface Architectural & SP

Features

amperage rating	0.125
Lamp Type	LED
lumens	4827
Number of Lamps	1
Wattage	35

Dimensions and Weight

Size	50.601 IN Length 3.6 IN Width 3.201 IN Height

Descriptions

Description	4SNLEDLD548SLUNVL840CD1U
extra long description	ECL 4SNLED-LD5-48SL-UNV-L840-CD1-U

Manufacturer Information

Brand	METALUX
GTIN	00080083800698
UPC	080083800698

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	Strip

Packaging

Carton	1
Weight Per each	4.98

Uses, Certifications, and Standards

Mounting	Strip
standard	CSA Listed