

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave. 76067-0000, TX Mineral Wells Phone: 940-325-5503

Fax: 940-325-5544



5008ME 1000W 480V Photocontrol

Nsi Industries

Catalog Number	5008ME
Manufacturer	Nsi Industries
Description	Turnlock Utility 480V Phototransistor With Delayed Response.
	Uses A Silicone Photo Sensor Instead Of A Standard CDS
	Photocell. For Use On Streets, Highways and Other Luminaries
	Equipped With Locking Type Receptacles, Where Most
	Stringentsurge Protection Is Needed.
Weight per unit	0.2000 (lbs/each)
Product Category	Lighting Photocells
_	

Features

Material	Polycarbonate	
supply voltage	480 VAC	
Timing Range	2 Minutes	
Warranty	5 Year	

Dimensions and Weight

Size	H=2.187	- W=3.187
OILO	11 21101	V V O 1 O 1

Descriptions

Description	1000W 480V PHOTOCONTROL
extra long description	TORK 5008ME TurnLock Utility 480V P
Features	UtilityGrade TurnLock, On 1-3fc, Off/On Ratio 5Max, Delay Resp, 1" Silicone Sensor, 480V, 7500W Tungsten, 4800VA Ballast
Long Description	TurnLock Utility 480V Phototransistor with delayed response. Uses a silicone photo sensor instead of a standard CdS photocell. For use on streets, highways and other luminaries equipped with locking type receptacles, where most stringentsurge protection is needed.
Product Type	Turnlock Utility 480V Phototransistor
Special Features	380 Joule MOV (Metal Oxide Varistor) Surge Arrestor - Locking Prongs - 1 Light Sensor
nufacturar Information	

Manufacturer Information

Brand	NSi
GTIN	00786261610201
Manufacturers Part Number	5008ME
UPC	786261610201

Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Туре	Delayed Response Utility Grade



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave. 76067-0000, TX Mineral Wells Phone: 940-325-5503 Fax: 940-325-5544

_	-	-	ĸ	-	,		
	a	۱.	ĸ	•			

Carton	1	
Weight Per each	0.2	

Uses, Certifications, and Standards

Application	Street-Highway Lighting
Enclosure	Polycarbonate
environmental conditions	-40 to + 140
Frequency Rating	50/60 Hz
Mounting	TWIST LOCK
Operating Temperature	-40 to + 140
standard	UL773