



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5351 SGL Recp 20A 125V S-Wire BR

Pass & Seymour/Legrand

| | |
|------------------|------------------------------------------------------------|
| Catalog Number | 5351 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Heavy-Duty Spec Grade Single Receptacle Side Wire 20A 125V |
| Weight per unit | 0.1656 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--------------------------------------------------|
| amperage rating | 20 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| Number of Wires | 3 |
| Outlet Type | Commercial, Indoor |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Brown |
|-------|-------|

Dimensions and Weight

| | |
|--------|------|
| Height | 3.68 |
| Width | 1.08 |

Descriptions

| | |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | SGL RECP 20A 125V S-WIRE BR |
| extra long description | P&S 5351 RECP SGL 20A 125V S-WIRE B |
| Long Description | Heavy-Duty Spec Grade Single Receptacle Side Wire 20A 125V |
| Product Type | Recp SGL 20A 125V S-Wire BN |
| Special Features | Auto-ground clip assures positive ground. Two drive screws anchor strap to back body and face where abrupt removal torque is greatest. Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength. Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility. One-piece brass triple-wire power contacts for lasting retention. |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007535105 |
| Manufacturers Part Number | 5351 |
| UPC | 785007535105 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | METALLIC FITTINGS |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.1656 |

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | CULUS, UL498, CSA C22.2 No. 42 |
| Temperature Rating | -40° - 60° C |