



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



54808 1AWG 2WAY Cop Conn

Abb Installation Products, Inc

Catalog Number	54808
Manufacturer	Abb Installation Products, Inc
Description	Copper Two-Way Splice, Long Barrel, Max 35KV, Wire Size 1 Awg, Length 2.0 Inches, Diameter 0.49 Inch, Tin Plated, Die Code 37, Die Color Code Green
Weight per unit	0.0490 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V

Material, Color, and Finish

Color	Green
Finish	Tin-Plated

Descriptions

Description	1AWG 2WAY COP CONN
extra long description	ABB 54808 2WAY CU SPLICE CONN LNGBR
Long Description	Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size 1 AWG, Length 2.0 Inches, Diameter 0.49 Inch, Tin Plated, Die Code 37, Die Color Code Green
Product Type	2WAY Cu Splice Conn LNGBRL 1 GRN
Special Features	Two-Way Connectors Provide High Pullout Values, are Easy to Insulate and Provide a Low-Resistance Connection of High Quality and Low Installed Cost

Manufacturer Information

Brand	COLOR-KEYED
GTIN	00786210548081
Manufacturers Part Number	54808
UPC	786210548081

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Splice Connector

Packaging

Carton	20
Weight Per each	0.049

Uses, Certifications, and Standards

Application	Applications certified to 600 V and recommended up to 35 kV
standard	UL E9809, CSA 4503 / UL E9809, CSA 4503