ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

552040407 20/4 Therm Wire 250'

Southwire Company

Catalog Number	552040407
Manufacturer	Southwire Company
Description	Thermostat Wire, Solid, 4 Conductors, #20 Awg Conductor Size, 150 V, 250 FT Overall Length, 0.132 In Outside Diameter, 0.006 In Insulation Thickness, Copper Conductor Material, Polypropylene Insulation Material, Red;White;Green;Blue, -20 °C Operating Temperature, +60 °C Operating Temperature, 16 LB/MFT
Weight per unit	0.0200 (lbs/ft)
Product Category	Jacketed Thermostat Wire & CBL

Descriptions

Description	20/4 THERM WIRE 250'
extra long description	SWC 552040407 TSTAT 20/4 CU CL2/CMH
Features	The Southwire Company 250 ft. 20/4 Brown Solid CU Thermostat Wire is manufactured using solid, copper conductors that have been paralleled and covered with a brown, PVC jacket. This wire can be used in temperatures up to 140 degree F. This thermostat and bell cable offers solid copper conductors with PVC insulation. This thermostat wire is also sunlight resistant.

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892352035
UPC	029892352035

Taxonomies, Classifications, and Categories

Category Description	Thermostat and Doorbell Wire

Availability

minimum qty	250

Packaging

Carton	250
Package	1000
Weight Per foot	0.02