


**LAMP HOLDERS****Traditional Lampholder  
75-150 Watt Par 38 Lamps****D23**

Catalog #: 5606-1

**APPLICATIONS**

For general outdoor lighting in wet, damp or dry locations  
 May be used with BELL® cluster covers and boxes

**PRODUCT FEATURES**

Rugged die cast construction  
 State-of-the-art powder coat finish provides maximum weatherability and scratch resistance  
 Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming  
 Extra long wire leads for easy hook-up  
 Porcelain socket  
 Inside Gasket  
 Multi-lingual instructions in each package  
 1/2 in. locknut  
 N/A

**UL LISTED**

Standard 1598

**CSA**

C22.2 No. 18

**GENERAL PRODUCT INFORMATION**

Color: White

**PRODUCT MEASUREMENTS**

Wt. Ea. (Lbs.): 0.464

**PACKAGING**

Package Type: Shrink  
 Std. Pkg.: 30  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 46.40  
 Ship Carton Length (in.): 16.19  
 Ship Carton Width (in.): 4.25  
 Ship Carton Height (in.): 8.50  
 Ctn Weight (Lbs.): 13.92  
 Pallet Qty: 4500.00  
 UPC Number: 050169560617  
 I2of5: 50050169560612