



660AAC TightSight® Clamp Meter with TRMS, Capacitance, Frequency



Product Resources

[Commercial/Industrial TightSight® Clamp Meters Brochure](#)
(PDF | 617K)

[61-763,61-765,61-773,61-775 Series Commercial/Industrial TightSight® Clamp Meters Instructions](#)
(PDF | 5640K | Rev 2)

[61-763 & 61-765 Clamp Meter Technical Manual](#)
(PDF | 305K | Rev 3)

Features

- 660 A True RMS clamps for a variety of industrial and commercial environments
- Unique TightSight® bottom display makes hard-to-reach measurements convenient
- Easy-to-read displays feature large numbers and green glowing backlight
- CAT IV rating for maximum safety
- Frequency, capacitance, peak, data hold, max/min

Models

Description	Catalog #
660AAC TightSight® Clamp Meter with TRMS, Capacitance, Frequency	61-763



660AAC TightSight® Clamp Meter with TRMS, Capacitance, Frequency



Product Resources

[Commercial/Industrial TightSight® Clamp Meters Brochure](#)

(PDF | 617K)

[61-763,61-765,61-773,61-775 Series](#)

[Commercial/Industrial TightSight® Clamp Meters Instructions](#)

(PDF | 5640K | Rev 2)

[61-763 & 61-765 Clamp Meter Technical Manual](#)

(PDF | 305K | Rev 3)

Features

- 660 A True RMS clamps for a variety of industrial and commercial environments
- Unique TightSight® bottom display makes hard-to-reach measurements convenient
- Easy-to-read displays feature large numbers and green glowing backlight
- CAT IV rating for maximum safety
- Frequency, capacitance, peak, data hold, max/min

Models

Description	Catalog #
660AAC TightSight® Clamp Meter with TRMS, Capacitance, Frequency	61-763