

# I/R Stylus® Alkaline Battery-Powered Pen Light

**Case Material:** Water-proof, machined aluminum case with anodized finish and non-slip, knurled grip comes in olive drab green

**Dimensions:** Length: 6.21 in. (15.17 cm) Diameter: 0.375 in. (0.95 cm)

**Weight:** 1.1 oz (31.19 grams)\*

**Light Source:** High-intensity “solid-state” 100,000 hour IR LED

**On/Off:** Features a momentary blink switch and constant “on”

**Run Time:** Up to 60 hours.

**Battery:** 3 “AAAA” size alkaline batteries.

- Features:**
- Waterproof
  - 880nm IR LED
  - Pocket clip
  - Sharp Spot, Glare Guard Protector (Included)
  - Compatible with most night vision goggles



**Approvals\*\*:** Most models meet applicable European Community Directives

**Warranty:** Limited lifetime warranty.

\*With battery (included in purchase).

\*\*See product for specific ratings.



Item	UPC	Part #
Stylus Accessory Pack OD Green I/R LED	080926-65089-3	65089
Glare Guard	080926-65031-2	65031
Lanyard with Push Button Slide	080926-72024-4	72024
AAAA Batteries – 6 pack	080926-65030-5	65030



# I/R Stylus® Alkaline Battery-Powered Pen Light

Case Material: Water-proof, machined aluminum case with anodized finish and non-slip, knurled grip comes in olive drab green

Dimensions: Length: 6.21 in. (15.17 cm) Diameter: 0.375 in. (0.95 cm)

Weight: 1.1 oz (31.19 grams)\*

Light Source: High-intensity “solid-state” 100,000 hour IR LED

On/Off: Features a momentary blink switch and constant “on”

Run Time: Up to 60 hours.

Battery: 3 “AAAA” size alkaline batteries.

- Features:
- Waterproof
  - 880nm IR LED
  - Pocket clip
  - Sharp Spot, Glare Guard Protector (Included)
  - Compatible with most night vision goggles



Approvals\*\*: Most models meet applicable European Community Directives

Warranty: Limited lifetime warranty.

\*With battery (included in purchase).

\*\*See product for specific ratings.



Item	UPC	Part #
Stylus Accessory Pack OD Green I/R LED	080926-65089-3	65089
Glare Guard	080926-65031-2	65031
Lanyard with Push Button Slide	080926-72024-4	72024
AAAA Batteries – 6 pack	080926-65030-5	65030

