

Project Name

Location

Prepared By



NUVO 65-701

4' LINEAR STRIP WHITE FINISH

Notes

(www) 18-27-2023 05:20:07

General

Status	Active
Fixture Type	Strip Light
Finish	White
Wattage	30W/40W/50W
Lumen Output	3900L-6750L
CCT (Kelvin)	3500K/4000K/5000K
IP Rating	IP20
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
Integrated Camera	No

Specifications

Technology	LED
Color Temperature	Warm to Cool White
CRI	80+
Voltage	120V-277V
Beam Angle	120
Rated Hours	50000
Operating Temperature	-20C (-4F) to +60C (+140F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming Only
Photocell or Sensor	Optional Add-On
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	3.56
Material	Steel

Dimensions

Height (in.)	3.27
Width (in.)	2.95
Length (in.)	48
Back Plate or Canopy Diameter (in.)	4.75

Compliance

Safety Listing	cULus - Certified
Location Rating	Damp
UL Application	Ceiling / Wall
ENERGY STAR	No
DLC Approved	Yes
DLC ID	PLK0WRSF76AD; PY93KEUH; S-KPXKB2
B.U.G. Rating	B2-U4-G2
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class A
Flicker Free	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5-Years
----------	---------