



6624GRTNK 6X6X24 N3R RT Wireway No Ko

Unity Manufacturing

Catalog Number	6624GRTNK
Manufacturer	Unity Manufacturing
Description	Slip-On Cover Trough, Slip On, Gray, Low Carbon Steel, 24 In Overall Length, 6 In Overall Height, 6 In Overall Width, Powder Coated, 11 LB
Weight per unit	11.0 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

Features

Knockouts	NO
-----------	----

Dimensions and Weight

Depth	6
Length	24
Width	6

Descriptions

Description	6X6X24 N3R RT WIREWAY NO KO
extra long description	UNT 6624GRTNK N3R SCREW COVER GUTTE
Special Features	For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket

Manufacturer Information

Brand	Unity
GTIN	00761515141908
UPC	761515141908

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	GRT Gutter Slip-On Cover Wiring Trough

Packaging

Carton	1
Weight Per each	11



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353

Uses, Certifications, and Standards

Enclosure
standard

NEMA 3R, IP32

UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily
To Provide A Degree Of Protection Against Rain, Sleet And
Damage From External Ice Formation, CSA C22.2 No. 26 Certified,
Type 3R, IEC 60529, RoHS Compliant