

MicroStream® Alkaline Battery-Powered LED Pen Light

Case Material: Type II MIL-SPEC abrasion and corrosion-resistant anodized aircraft aluminum

Dimensions: Length: 3.5 inches (90 mm) Diameter: 0.6 inches (15 mm)

Weight: 1.04 oz. (29.7 grams) with battery

Light Source: 0.5 Watt High-Flux LED; 30,000 hours rated LED life

Light Output: Up to 20 Lumens Typical

On/Off: Push Button Tail switch

Run Time: Up to 1.5 hours of regulated runtime

Battery: 1 "AAA " alkaline battery

- Features:
- Proprietary Micro Optical System (MOS), for optimized output and runtime
 - Battery-Booster" electronics to provide a super-bright beam.
 - An internal polymer body liner and shock proof switch housing allow for operation under the most extreme conditions
 - O-Ring Sealed, shock proof and drop tested construction
 - Water resistant
 - High Strength "Break Away" safety lanyard.
 - Unbreakable pocket clip

Approvals**: Most models meet applicable European Community Directives.

Warranty: Limited lifetime warranty.

**With batteries (included in purchase)
Made in China*



Item	UPC	Part #
MicroStream Black with White LED	080926-66318-3	66318

