



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 72N2 Scotchcast Inline Splice Kit, 0-600V *Minnesota Mining (3M)*

Catalog Number	72N2
Manufacturer	Minnesota Mining (3M)
Description	3M™ Scotchcast™ 72 N Series Inline Splice Kit Is A 1 KV Rated, Rigid Body Splice Designed to Join Signal and Control Cables. It Fits Shielded or Unshielded Constructions Of Plastic or Rubber Jacketed Cables. It Is Perfect For Inline Splicing Of Shielded or Unshielded Cables, Underground Systems, Joining Of Cable Reel Ends, Direct Burial Applications, Repair Of Cable Failures and Dig Ins.
Weight per unit	1.3 (lbs/each)
Product Category	Splicing & Terminating Kits

### Descriptions

Description	SCOTCHCAST INLINE SPLICE KIT, 0-600V
extra long description	3M 7100007449 3M™ Scotchcast™ Inlin
Features	3M™ Scotchcast™ 72 N Series Inline Splice Kit helps in sealing collars or splice body ends, and the jumper wire with clips offers solderless shield continuity on shielded cables. RoHS 2011/65/EU Compliant?.
Long Description	3M™ Scotchcast™ 72 N Series Inline Splice Kit is a 1 kV rated, rigid body splice designed to join signal and control cables. It fits shielded or unshielded constructions of plastic or rubber jacketed cables. It is perfect for inline splicing of shielded or unshielded cables, underground systems, joining of cable reel ends, direct burial applications, repair of cable failures and dig ins.
Product Type	3M™ Scotchcast™ Inline Splice Kits 72-N Series

### Manufacturer Information

Brand	Scotchcast
GTIN	00054007106258
Manufacturers Part Number	72N2
UPC	054007106258

### Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	Resin Splice

### Packaging

Carton	1
Package	10
Weight Per each	1.287