

Decorator Standard Grade Switches

Single-Pole, 3-Way, 4-Way
15A, 120/277V/AC

FEATURES


- Redesigned paddle for easier actuation and quiet operation.
- Thermoplastic rocker, top and backbody are virtually unbreakable, promising years of durable performance.
- Ultrasonic welding and integrated construction of the strap and body provide superior integrity.
- Backwire clamps on the side terminals provide for easy installation of #12 and #14 AWG wire.
- Push-in terminals accept #14 AWG solid wire.
- Stippled ground screw terminal standard.
- 120/277V/AC rating ideal for fluorescent lighting fixtures and a broad variety of applications.
- Long, broad mounting strap virtually eliminates floating installations.
- Patented built-in wire stripper for #12 and #14 AWG wire to speed installation.
- Tri-combo screws accept Slotted, Phillips, and Robertson-head tools for installation flexibility.
- Lighted switches glow in “off” position.




7501

Decorator Switches

15A 120/277V/AC; Back Wire, Side Wire & Push Wire

Description	Color Suffix	Catalog No.	
Single-Pole	A, B, BK, GY, LA, V, W	□ 7501__	•
3-Way	A, B, BK, GY, LA, V, W	□ 7503__	•
4-Way	A, B, BK, GY, LA, V, W	□ 7504__	
Lighted Single-Pole	A, LA, V, W	□ 7511__	
Lighted 3-Way	A, LA, V, W	□ 7513__	

 cULus Listed to UL20, file no. E18704; 7504 & 7514 also UL verified to Federal Spec WS-896E

Heavy Duty Grade Toggle Switches

Single-Pole, 3-Way
15A, 120/277V/AC

FEATURES

- Small toggle switch blends with standard grade toggles.
- Larger contacts and robust design for extended switch life.
- Backwire clamps on the side terminals provide for easy installation of #12 and #14 wire.
- Side wire terminals accept up to #10 solid wire.
- Heavy duty cam action mechanism ensures quiet switch action.
- 120/277V/AC rating ideal for fluorescent lighting fixtures and a broad variety of applications.
- Long, broad steel mounting strap zinc-plated for corrosion resistance, virtually eliminates floating installations.
- Patented built-in wire stripper for #12 and #14 wire to speed installation.
- Ground screw terminal standard.
- Stippled line and ground contacts standard.
- Tri-Combo head mounting and terminal screws ease installation.



CSB115ST

Heavy Duty Toggle Switches

15A 120/277V/AC; Back & Side Wire

Description	Color Suffix	Catalog No.	
Single-Pole	A, B, LA, V, W	□ CSB115ST__	•
3-Way	A, B, LA, V, W	□ CSB315ST__	•

  cULus Listed to UL20, file no. E18704; NOM certified

Color Ordering Information: For ordering devices, include Cat. No. followed by the color code: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

Dimensional Information: B-60

Specification Information: Please visit www.cooperwiringdevices.com

 **NAFTA Compliant:** See page F-21