
NON-NEMA 3 WIRE PLUG, YELLOW

7554SS | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Plug 3wire 15amp 125volt 10amp 250v

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: Plug

Number Of Wires: 3

Special Features: Non-NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 39121403

DIMENSIONS

Diameter (US): 1.531"

Length (US): 1.105"

TECHNICAL INFORMATION

Amps: 15A

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

