

Stinger® DS LED Rechargeable Flashlight

Case Material: 6000 series machined aircraft aluminum with non-slip rubberized comfort grip and anti-roll rubber ring.

Dimensions: Length: 8.85 in. (22.48 cm) Diameter: Major Diameter: 1.62 in. (4.11 cm)
 Body Diameter: 1.17 in. (2.97 cm)

Weight: 12.8 oz (352 grams)*

Lens: Unbreakable polycarbonate lens with scratch-resistant coating

Light Source: C4 LED technology, impervious to shock with a 50,000 hour lifetime.

Light Output: Up to 18,000 candela (peak beam intensity); up to 160 lumens. Deep-dish parabolic reflector produces a long range targeting beam with optimum peripheral illumination. Optimized electronics provides regulated intensity.

On/Off: Dual switch technology: Independently working push button tailcap switch or head switch. Access any of the three variable lighting modes and strobe via the tail cap or the head-mounted switch

Run Time: High brightness: Up to 1.75 continuous hours .
 Medium brightness: Up to 3.50 continuous hours
 Low brightness: Up to 6.75 continuous hours
 Strobe: Up to 5.50 continuous hours.

Battery: 3-Cell, 3.6-Volt Nickel-cadmium sub-C battery is rechargeable up to 1000 times

Charging: Ten hours to fully recharge on 100V, 120V, 230V or 240V AC, or 12V DC; 2.5-hour fast charger or PiggyBack® charger model available

Features: • Dual switch technology • Anti-roll ring included • LED charge-continuity indicator, compact
 • Snap-in charger holder that mounts in any position • Serialized for positive identification

Approvals**: Most models meet applicable European Community Directives.

Warranty: Limited lifetime warranty

*With battery (included in purchase).

**See product for specific ratings.



Item	UPC	Part #
<i>Steady Charge</i>		
Stinger DS LED w/ 230V AC/DC	080926-75825-4	75825
Stinger DS LED w/ 240V AC/DC	080926-75829-2	75829
Stinger DS LED w/ 120V AC/DC	080926-75813-1	75813
Stinger DS LED w/ 100V AC/DC	080926-75818-6	75818
Stinger DS LED w/ 230V AC	080926-75824-7	75824
Stinger DS LED w/ 240V AC	080926-75828-5	75828
Stinger DS LED w/ 120V AC	080926-75811-7	75811
Stinger DS LED w/ 100V AC	080926-75817-9	75817
Stinger DS LED w/ 12V DC	080926-75812-4	75812
<i>Steady Charge PiggyBack</i>		
Stinger DS LED w/ 230V AC/DC	080926-75839-1	75839
Stinger DS LED w/ 240V AC/DC	080926-75843-8	75843
Stinger DS LED w/ 120V AC/DC	080926-75832-2	75832
Stinger DS LED w/ 100V AC/DC	080926-75846-9	75846
Stinger DS LED w/ 230V AC	080926-75838-4	75838
Stinger DS LED w/ 240V AC	080926-75842-1	75842
Stinger DS LED w/ 120V AC	080926-75833-9	75833
Stinger DS LED w/ 100V AC	080926-75821-6	75821
Stinger DS LED w/ 12V DC	080926-75834-6	75834

Item	UPC	Part #
<i>Fast Charge</i>		
Stinger DS LED w/ 230V AC/DC	080926-75827-8	75827
Stinger DS LED w/ 240V AC/DC	080926-75831-5	75831
Stinger DS LED w/ 120V AC/DC	080926-75835-3	75835
Stinger DS LED w/ 100V AC/DC	080926-75820-9	75820
Stinger DS LED w/ 230V AC	080926-75826-1	75826
Stinger DS LED w/ 240V AC	080926-75830-8	75830
Stinger DS LED w/ 120V AC	080926-75814-8	75814
Stinger DS LED w/ 100V AC	080926-75819-3	75819
Stinger DS LED w/ 12V DC	080926-75815-5	75815
<i>Fast Charge PiggyBack</i>		
Stinger DS LED w/ 230V AC/ DC	080926-75841-4	75841
Stinger DS LED w/ 240V AC/ DC	080926-75845-2	75845
Stinger DS LED w/ 120V AC/ DC	080926-75816-2	75816
Stinger DS LED w/ 100V AC/ DC	080926-75847-6	75847
Stinger DS LED w/ 230V AC	080926-75840-7	75840
Stinger DS LED w/ 240V AC	080926-75844-5	75844
Stinger DS LED w/ 120V AC	080926-75836-0	75836
Stinger DS LED w/ 100V AC	080926-75822-3	75822
Stinger DS LED DC	080926-75837-7	75837
<i>(WITHOUT CHARGER)</i>		
Stinger DS LED	080926-75810-0	75810
<i>See reverse for additional images</i>		



