



INDUSTRIAL
COMMERCIAL
RESIDENTIAL

V-9 ELECTRICAL ACCESSORIES

MATERIAL CHARACTERISTICS

Cat. No.'s 87 & 88

Environmental:

Flammability
per UL 94
requirements,
V2 rated.

Temperature Rating:
-40°C to 80°C.

Bushings:

Meets flammability
requirements per
UL 94, VO rated.

Temperature Rating:

76 and 77:

-20°C to 70°C,

28 and 30:

-20°C to 60°C.



2529C



2530



7949



756



76



28

Miscellaneous Accessories

Plate Screws and Key

FEATURES

- All screws are #6-32.

Spanner Head

Description	Finish	Length	Catalog No.
Tamper resistant	Chromium	13/32" (10.319mm)	2529C
Key for 2529C	—		2530

Metal Switch Lever Guard

FEATURES

- Nickel finish
- For flush tumbler switch levers
- Attaches to standard plates by the plate screws

Metal Switch Lever Guard

Description	Catalog No.
Switch lever guard with 1/4 padlock holes	7949

Sub-Frame and Blank Insert

Description	Color	Catalog No.
Blank insert and strap for standard switch plate	Brown	756B
	Gray	756GY
	Ivory	756V
	Light Almond	756LA
	White	756W

Bushings

FEATURES

- Provide smooth protective surface for cords or wires passing through knockouts.

Bushings

Description	Knockout Size	Inside Diameter	Outside Diameter	Groove	Catalog No.
Rubber	0.375" (9.525mm)	0.375" (9.525mm)	0.75" (19.05mm)	0.50" (12.70mm)	76
Rubber	0.50" (12.70mm)	0.50" (12.70mm)	1.031" (26.19mm)	0.875" (22.225mm)	77
Plastic with Lock Nut	0.50" (12.70mm)	0.50" (12.70mm)	—	—	28
Plastic with Lock Nut	0.75" (19.05mm)	0.75" (19.05mm)	—	—	30



INDUSTRIAL
COMMERCIAL
RESIDENTIAL

V-9 ELECTRICAL ACCESSORIES

MATERIAL CHARACTERISTICS

Cat. No.'s 87 & 88

Environmental:

Flammability
per UL 94
requirements,
V2 rated.

Temperature Rating:
-40°C to 80°C.

Bushings:

Meets flammability
requirements per
UL 94, VO rated.

Temperature Rating:

76 and 77:

-20°C to 70°C,

28 and 30:

-20°C to 60°C.



2529C



2530



7949



756



76



28

Miscellaneous Accessories

Plate Screws and Key

FEATURES

- All screws are #6-32.

Spanner Head

Description	Finish	Length	Catalog No.
Tamper resistant	Chromium	13/32" (10.319mm)	2529C
Key for 2529C	—		2530

Metal Switch Lever Guard

FEATURES

- Nickel finish
- For flush tumbler switch levers
- Attaches to standard plates by the plate screws

Metal Switch Lever Guard

Description	Catalog No.
Switch lever guard with 1/4 padlock holes	7949

Sub-Frame and Blank Insert

Description	Color	Catalog No.
Blank insert and strap for standard switch plate	Brown	756B
	Gray	756GY
	Ivory	756V
	Light Almond	756LA
	White	756W

Bushings

FEATURES

- Provide smooth protective surface for cords or wires passing through knockouts.

Bushings

Description	Knockout Size	Inside Diameter	Outside Diameter	Groove	Catalog No.
Rubber	0.375" (9.525mm)	0.375" (9.525mm)	0.75" (19.05mm)	0.50" (12.70mm)	76
Rubber	0.50" (12.70mm)	0.50" (12.70mm)	1.031" (26.19mm)	0.875" (22.225mm)	77
Plastic with Lock Nut	0.50" (12.70mm)	0.50" (12.70mm)	—	—	28
Plastic with Lock Nut	0.75" (19.05mm)	0.75" (19.05mm)	—	—	30