



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7803 30A 3P 3 PH Ac Motor

Pass & Seymour/Legrand

Catalog Number	7803
Manufacturer	Pass & Seymour/Legrand
Description	Three Pole, Three Phase Ac Manual Motor Controller, Suitable As Motor Disconnect - 10KA @ 600VAC, 30A Max. Class J Fuse.
Weight per unit	0.3300 (lbs/each)
Product Category	Misc Wiring Devices

Features

actuator	Toggle
amperage rating	30
connection	Side & Back Wired
load	30A
Number of Phases	3.0
operating cycles	50000
Poles	3 Pole
Voltage	600.0 V
Voltage Rating	600
Wire Size	#14 - #10 Awg

Dimensions and Weight

Size	1.7538" Depth x 1.825" Width x 2.375" Height
------	----------------------------------------------

Descriptions

Description	30A 3P 3 PH AC MOTOR
extra long description	P&S 7803MD 30A 3P 3 PH AC MOTOR
Long Description	Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.
Product Type	30A 3P 3 PH Ac Motor
Special Features	Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267686
Manufacturers Part Number	7803MD
UPC	785007267686

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	Manual Controller

Trade Size

Amperage	30.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Package 10

Weight Per each 0.33

Uses, Certifications, and Standards

Application Commercial/Industrial

environmental conditions UL94 V2

Frequency Rating 60Hz

Mounting BOX

Operating Temperature Maximum continuos +75°C, minimum -40°C

standard CULUS, CSA Listed, UL Listed