




# Fluorescent Lampholders Medium & Tall Profile

## Medium Profile - T8 & T12



**80-1252**  
Shunted for Instant Start Ballast Applications

**80-1253**  
Rapid Start Applications  
1 1/2" H x 1 1/4" W x 3/4" Dia.  
660W-600V



**80-1254**  
Rapid Start Applications  
Slide-On Mounting, 20 Gauge Slots Upper & Lower

**80-2127** w/Nut & Screw  
**80-1255, 80-1256**  
Shunted for Instant Start Ballast Applications  
Slide-On Mounting, 20 Gauge Slots Upper & 18 Gauge Lower  
1 5/8" H x 1 1/4" W x 3/4" Dia.  
660W-600V



**80-1245**  
Shunted for Instant Start Ballast Applications

**80-1246**  
Rapid Start Applications, Tall Rotary Locking T8/T12  
Used in Troffer and Wrap Fixtures for  
Retro Fit Kits/Replacements Snap Wing Mounting  
1 3/4" H x 1 1/8" W x 7/8" Dia.  
Made from Urea 660W-600V



**80-1257**  
Rapid Start Applications

**80-1258**  
Shunted for Instant Start Ballast Applications  
1 9/16" H x 1 1/4" W x 3/4" Dia.  
660W-600V



**80-1247**  
Tall Standard Twist-In Used in Strip Fixtures for  
Rapid Start Applications, Slide-On Mounting  
20 Gauge Slots Upper & Lower  
2" H x 1 1/4" W x 3/4" Dia.  
Made from Urea 660W-600V



**80-1248**  
Tall Standard Twist-In Externally Shunted Used in Strip Fixtures for  
Instant Start Ballasts, Slide-On Mounting  
20 Gauge Slots Upper & 18 Gauge Lower  
2" H x 1 1/4" W x 3/4" Dia.  
Made from Urea 660W-600V

Instant - Shunted  
Rapid - Not Shunted

**SOCKETS & LAMP HOLDERS**