



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



814DC2 4" 90 Degree Flexible Metal Conduit Conn

Nsi Industries

Catalog Number	814DC2
Manufacturer	Nsi Industries
Description	90 Degree Connector, Zinc Die Cast, Flex Size 4"
Weight per unit	6.0 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	90 DEG
Connector Type	FMC
Material	Cast Zinc
media	Yes

Material, Color, and Finish

Finish	As Cast
--------	---------

Dimensions and Weight

Size	4
------	---

Descriptions

Description	4" 90 DEGREE FLEXIBLE METAL CONDUIT CONN
extra long description	BPT 814-DC2 4" FMC 90 DEGREE CONN
Long Description	90 Degree Connector, Zinc Die Cast, Flex Size 4"
Product Type	4" FMC 90 Degree Conn

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747158147
Manufacturers Part Number	814-DC2
UPC	781747158147

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	4
------------	---

Packaging

Carton	1
Weight Per each	6

Uses, Certifications, and Standards

Application	90 Degree Connector used to connect Flexible Metal Conduit to box enclosure.
standard	UL, CSA