



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



850SP [25]3/8 90` Snapin SQZ *Bridgeport Fittings*

| | |
|------------------|--------------------------------------------------|
| Catalog Number | 850SP |
| Manufacturer | Bridgeport Fittings |
| Description | E-Z Lock 90 Degree Connector Double Screw Design |
| Weight per unit | 0.0880 (lbs/each) |
| Product Category | BX, MC, Armored Cable Fittings |

Features

| | |
|----------|---------------|
| Material | Zinc Die Cast |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|-----|
| Size | 3/8 |
|------|-----|

Descriptions

| | |
|------------------------|--------------------------------------------------|
| Description | [25]3/8 90` SNAPIN SQZ |
| extra long description | BPT 850SP 3/8" SNAP-IN 90 DEG FMC C |
| Features | Time Saver: Fast and EZ to Use. EZ to Reuse! |
| Long Description | E-Z LOCK 90 Degree Connector Double Screw Design |
| Product Type | 3/8" Snap-In 90 Deg FMC Conn |
| Special Features | HCF |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747718013 |
| Manufacturers Part Number | 850SP |
| UPC | 781747718013 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------------|
| Category Description | FORM 7, 8, CONDULETS, COVERS, & GASKETS |
| Type | Double Screw |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.088 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | 90degree Connector for use with 3/8" Flexible Metal Conduit. Non-Insulated. Recommended cable types: Diameter for 12/2 (.550" 0 min) to 10/3 (.610" 0 max) |
| standard | UL |