



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **8644XSCHC Encl 8X6X4 N4X SS CH CLMP CVR**

*Cooper B-Line/Cable Tray*

|                  |                                                                                                                                                                                                                               |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | 8644XSCHC                                                                                                                                                                                                                     |
| Manufacturer     | Cooper B-Line/Cable Tray                                                                                                                                                                                                      |
| Description      | Eaton B-Line Series Jic Panel Enclosure, 8" Height, 4" Length, 6" Width, Nema 4X, Hinged Cover, 4XSCHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket |
| Weight per unit  | 4.7 (lbs/each)                                                                                                                                                                                                                |
| Product Category | Nema Types 4 & 4X Metallic Enc                                                                                                                                                                                                |

### **Features**

|               |                                   |
|---------------|-----------------------------------|
| dimensions    | 4.0000 IN X 6.0000 IN X 8.0000 IN |
| Mounting Type | Wall                              |

### **Material, Color, and Finish**

|       |      |
|-------|------|
| Color | Gray |
|-------|------|

### **Dimensions and Weight**

|      |                                                |
|------|------------------------------------------------|
| Size | 6.00 In Width X 4.00 In Depth X 8.00 In Height |
|------|------------------------------------------------|

### **Descriptions**

|                        |                                                                                                                                                                                                                                         |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | ENCL 8X6X4 N4X SS CH CLMP CVR                                                                                                                                                                                                           |
| extra long description | B-LINE 864-4XSCHC TYPE 4X SSL JIC C                                                                                                                                                                                                     |
| Features               | Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes. |
| Long Description       | Eaton B-Line series JIC panel enclosure, 8" height, 4" length, 6" width, NEMA 4X, Hinged cover, 4XSCHC enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket           |
| Product Type           | Type 4X SSL Jic Continuous Hinge CVR Enc, 8X6X4                                                                                                                                                                                         |
| Special Features       | Cont. piano hinge,panel mount prov.,s.s.doorclamps                                                                                                                                                                                      |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782051702941 |
| Manufacturers Part Number | 864-4XSCHC     |
| UPC                       | 782051702941   |

### **Taxonomies, Classifications, and Categories**

|                      |                      |
|----------------------|----------------------|
| Category Description | STEEL JUNCTION BOXES |
| Type                 | JIC panel enclosure  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Weight Per each | 4.737 |

## Uses, Certifications, and Standards

|             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | Ind Facilities & Factories - Mfg. Process Electrification and ControlCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsInd Facilities & Factories - Facility: Lighting and Lighting ControlsInd Facilities & Factories - Facility: Automation and MonitoringInd Facilities & Factories - Industrial Facilities/Factories - OtherInd Facilities & Factories - Facility: Power Distribution and ControlInd Facilities & Factories - Facility: Critical PowerInd Facilities & Factories - Facility |
| Mounting    | EXTERNAL FEET, WALL                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| standard    | NEMA,CSA C22.2.,UL 50                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |