



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1501 North Cypress Street  
72114-0000, AR N. Little Rock  
Phone: 501-945-9398  
Fax: 501-508-2426



## 885GRY Radiant 15A 125V Duplex Recp Gy

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | 885GRY   |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Take A Step Up From The Standard. This Duplex Outlet Installs Easily For The Basic Power Every Home Needs, While Elevating Your Space With The Sleek, Clean Lines Of Radiant Registered For A Sophisticated Look. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately. |
| Weight per unit  | 0.1400 (lbs/each)  |
| Product Category | Gen Purpose Recept & Surge Pro   |

### Features

|                     |                                  |
|---------------------|----------------------------------|
| gang                | 2                                |
| indoor/outdoor      | Indoor                           |
| insulation          | False                            |
| media               | Yes                              |
| Mounting Type       | Box                              |
| Number of Gangs     | 1.0                              |
| Number of Wires     | 3                                |
| orientation         | Vertical                         |
| Outlet Type         | Tamper-Resistant, Straight Blade |
| Poles               | 2                                |
| Voltage             | 120.0 V, 125.0 V                 |
| Wall Plate Included | NO                               |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | Matte |
|--------|-------|

### Dimensions and Weight

|           |       |
|-----------|-------|
| Size      | 4.25" |
| Thickness | 1.3"  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1501 North Cypress Street  
72114-0000, AR N. Little Rock  
Phone: 501-945-9398  
Fax: 501-508-2426

## Descriptions

|                        |  |
|------------------------|--|
| Description            | RADIANT 15A 125V DUPLEX RECP GY  |
| extra long description | P&S 885GRY RADIANT 15A/125V DUP REC  |
| Features               | Decorator Style  |
| Long Description       | Take a step up from the standard. This duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. |
| Product Type           | Radiant 15A/125V Dup Recep Gry   |
| Special Features       | High impact resistant, extra long strap, quick loop wire aid, long term blade retention  |

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007885088   |
| Manufacturers Part Number | 885-GRY          |
| UPC                       | 785007885088     |

## Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type                 | Outlet               |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 10   |
| Package         | 200  |
| Weight Per each | 0.14 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Residential/Commercial                  |
| environmental conditions | 95% (relative humidity, non-condensing) |
| Mounting                 | WALL                                    |
| nema rating              | 15A                                     |
| standard                 | CULUS, UL, UL 498                       |