



9331-EWC2

9331-EWK











9363-EWC2


9363-EWK

9366-EWK

9368-EWK

Ears & Wing Brackets

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
14.0	9331-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	2-½	2-3/8	3-¼	38500	100	30
14.0	9331-EWC2	 Ears, wing brackets, 2 wire clamps - factory installed	2-½	2-3/8	3-¼	38510	100	33
14.0	9331-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	2-½	2-3/8	3-¼	38511	100	31
16.0	9363-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	2-27/32	2-3/8	3-¼	10572	100	32
16.0	9363-EWC2	 Ears, wing brackets, 2 wire clamps - factory installed	2-27/32	2-3/8	3-¼	10573	100	36
16.0	9363-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	2-27/32	2-3/8	3-¼	10578	100	33
18.0	9366-EW	 Wide body box, ears, wing brackets, Speed Klamps™ - bulk packed *Requires oversized device/receptacle plate	2-27/32	2-¾	3-¼	77001	100	34
18.0	9366-EWK	 Wide body box, ears, wing brackets, Speed Klamps™ - factory installed *Requires oversized device/receptacle plate	2-27/32	2-¾	3-¼	77002	100	35
18.0	9368-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	3-3/16	2-3/8	3-¼	76002	100	32
18.0	9368-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	3-3/16	2-3/8	3-¼	76001	100	34



9303-H

9367-E

1TP




9318

9319

9320

9322

Miscellaneous

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
6.0	9303-H	Side mount hanger, ¼" offset, not UL® listed	1-1/16	2-¼	3-5/8	10021	100	20
16.0	9367-E	 Side cube box, ears	1-11/16	2-3/8 open 4-15/16 overall	3-¼	75600	50	17
16.0	9367-EW	 Side cub box, ears, wing brackets	1-11/16	2-3/8 open 4-15/16 overall	3-¼	75601	50	18
—	1TP	 Metal template for single gang old work box: Series 9331-E, 9363-E, & 9368-E	0.062	4	6	88015	1	1

Handy Box & Covers

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
12.5	9318	Handy Box surface mounted box with side and bottom cable openings	2	2-¼	4-3/16	10140	100	28
—	9319	Handy Box switch cover, not UL® listed	—	2-¼	4-¼	10145	100	8
—	9320	Handy Box duplex outlet cover, not UL® listed	—	2-3/16	4-¼	10146	100	7
—	9322	Handy Box blank cover, not UL® listed	—	2-3/16	4-3/16	10148	100	7

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.

 Old Work/Manufactured Housing Boxes

 Flush-Device Box
UL File No. E30594

Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
9361-ESK	E168/7010-8/7020-8	N/A	N/A	N/A	N/A	N/A
9363-E	6060-02	N/A	N/A	N/A	N/A	N/A
9363-EK	6060-02	N/A	N/A	N/A	N/A	N/A
9363-EW	6010-402/6060-402	114-OW	N/A	N/A	N/A	N/A
9363-EWK	6010-402/6060-402	114-OW	N/A	N/A	N/A	N/A
9364	4060-02	N/A	N/A	N/A	N/A	N/A
9364-16/16K	4060-9402	N/A	N/A	N/A	N/A	N/A
9364-16G/16GK	N/A	N/A	N/A	N/A	N/A	N/A
9364-BH/BHK	4060-9502	N/A	N/A	N/A	N/A	N/A
9364-BHG/BHGK	N/A	N/A	N/A	N/A	N/A	N/A
9364-K	4060-02	N/A	N/A	N/A	N/A	N/A
9365-N	4160-C	N/A	N/A	N/A	N/A	N/A
9365-NK	4160-C/N40712RC	N/A	N/A	N/A	N/A	N/A
9366-EK	N/A	N/A	N/A	N/A	N/A	N/A
9366-EW	N/A	N/A	N/A	BH118R	N/A	N/A
9366-EWK	N/A	N/A	N/A	BH118R	N/A	N/A
9367-E	6000-402/E01-712	N/A	B117RSW	B117RSW	N/A	N/A
9367-EW	6000-402	N/A	B117RSW	B117RSW	N/A	N/A
9368-E	N/A	N/A	N/A	N/A	N/A	N/A
9368-EK	N/A	N/A	N/A	N/A	N/A	N/A
9368-EW	6070-4/E214	N/A	B120R	BH118R	EZ21S0	S118W
9368-EWK	6070-4/E214	N/A	B120R	BH118R	EZ21S0	S118W
9372-NMHK	N/A	N/A	N/A	N/A	N/A	N/A
RD-42	RD-30	N/A	B234ADJC/RDS-30	N/A	N/A	P242RRD
RD-42SS	N/A	N/A	N/A	N/A	N/A	P242SRD

fiberglassBOX™: Paddle Fan Support Boxes

Allied Moulded	Westinghouse	Arlington	Raco	Carlton PC	Steel City (T&B)	Carlton PH	Reiker (P&S)	Slater (P&S)
9335-NFR/NKFR	N/A	FB417S/FBS420S	N/A	N/A	N/A	N/A	N/A	N/A
9336-NKFR	01040-11	FBS415S	N/A	N/A	N/A	N/A	N/A	N/A
9350-FAN/FANB	N/A	N/A	927/928	N/A	N/A	4070-CFB-BHL	65521/85502	N/A
9350-FRBKOW	N/A	FBRS420R	934	N/A	N/A	N/A	22200	N/A
9350-KFR	N/A	FB423/FBS420	7120/299	B720-SHK	54171-CFB	CFB-16	44400/55528	S1-6-FAN
9351-NFR/NKFR	01240-11	FB417S	294-1	BH525L/BH525LP	54171-F-CFB	4170-CFB	55020/55025	S1-20-RFAN
9364-FAN/FANB	01525/ 01100/ 01010	N/A	925/926	MB715H	N/A	N/A	N/A	N/A
9364-FRBKOW	N/A	N/A	935	MB715RH	54151CFB-BHL-OW	N/A	33310/83300	N/A
9364-KFR	01050-11	FBS426	N/A	N/A	N/A	N/A	33303/55505	N/A
9365-NKFR	01250-11	N/A	N/A	BH525L	N/A	N/A	55015/33303	N/A
9369-FB	01020-11	FBS426	296-1	MB715S	54151-CFB	N/A	N/A	N/A
9369-FBH	01250	FBS415S	N/A	N/A	N/A	N/A	N/A	N/A
9369-FRBKB	0152511	FBRS415	926-1	MB715H	54151CFB-BHL	N/A	55501	N/A
9370-FR	01030	FB407	N/A	N/A	N/A	N/A	N/A	S1-09-FAN
9373-FR	02000	FB443	7120	CFB-16	N/A	N/A	N/A	S1-16-FAN
9375-FR	02525	FB442/FB412	7120	CFB-12	N/A	N/A	N/A	N/A



9331-EWC2











9331-EWK


9363-EWC2

9363-EWK

9366-EWK

9368-EWK

	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
Ears & Wing Brackets	14.0	9331-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	2-½	2-3/8	3-¼	38500	100	30
	14.0	9331-EWC2	 Ears, wing brackets, 2 wire clamps - factory installed	2-½	2-3/8	3-¼	38510	100	33
	14.0	9331-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	2-½	2-3/8	3-¼	38511	100	31
	16.0	9363-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	2-27/32	2-3/8	3-¼	10572	100	32
	16.0	9363-EWC2	 Ears, wing brackets, 2 wire clamps - factory installed	2-27/32	2-3/8	3-¼	10573	100	36
	16.0	9363-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	2-27/32	2-3/8	3-¼	10578	100	33
	18.0	9366-EW	 Wide body box, ears, wing brackets, Speed Klamps™ - bulk packed <i>*Requires oversized device/receptacle plate</i>	2-27/32	2-¾	3-¼	77001	100	34
	18.0	9366-EWK	 Wide body box, ears, wing brackets, Speed Klamps™ - factory installed <i>*Requires oversized device/receptacle plate</i>	2-27/32	2-¾	3-¼	77002	100	35
	18.0	9368-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	3-3/16	2-3/8	3-¼	76002	100	32
	18.0	9368-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	3-3/16	2-3/8	3-¼	76001	100	34



9303-H

9367-E




1TP

9318

9319

9320

9322

	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
Miscellaneous	6.0	9303-H	Side mount hanger, ¼" offset, not UL® listed	1-1/16	2-¼	3-5/8	10021	100	20
	16.0	9367-E	 Side cube box, ears	1-11/16	2-3/8 open 4-15/16 overall	3-¼	75600	50	17
	16.0	9367-EW	 Side cub box, ears, wing brackets	1-11/16	2-3/8 open 4-15/16 overall	3-¼	75601	50	18
	—	1TP	 Metal template for single gang old work box: Series 9331-E, 9363-E, & 9368-E	0.062	4	6	88015	1	1

	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
Handy Box & Covers	12.5	9318	Handy Box surface mounted box with side and bottom cable openings	2	2-¼	4-3/16	10140	100	28
	—	9319	Handy Box switch cover, not UL® listed	—	2-¼	4-¼	10145	100	8
	—	9320	Handy Box duplex outlet cover, not UL® listed	—	2-3/16	4-¼	10146	100	7
	—	9322	Handy Box blank cover, not UL® listed	—	2-3/16	4-3/16	10148	100	7

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.

 Old Work/Manufactured Housing Boxes

 Flush-Device Box
UL File No. E30594

Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
9361-ESK	E168/7010-8/7020-8	N/A	N/A	N/A	N/A	N/A
9363-E	6060-02	N/A	N/A	N/A	N/A	N/A
9363-EK	6060-02	N/A	N/A	N/A	N/A	N/A
9363-EW	6010-402/6060-402	114-OW	N/A	N/A	N/A	N/A
9363-EWK	6010-402/6060-402	114-OW	N/A	N/A	N/A	N/A
9364	4060-02	N/A	N/A	N/A	N/A	N/A
9364-16/16K	4060-9402	N/A	N/A	N/A	N/A	N/A
9364-16G/16GK	N/A	N/A	N/A	N/A	N/A	N/A
9364-BH/BHK	4060-9502	N/A	N/A	N/A	N/A	N/A
9364-BHG/BHGK	N/A	N/A	N/A	N/A	N/A	N/A
9364-K	4060-02	N/A	N/A	N/A	N/A	N/A
9365-N	4160-C	N/A	N/A	N/A	N/A	N/A
9365-NK	4160-C/N40712RC	N/A	N/A	N/A	N/A	N/A
9366-EK	N/A	N/A	N/A	N/A	N/A	N/A
9366-EW	N/A	N/A	N/A	BH118R	N/A	N/A
9366-EWK	N/A	N/A	N/A	BH118R	N/A	N/A
9367-E	6000-402/E01-712	N/A	B117RSW	B117RSW	N/A	N/A
9367-EW	6000-402	N/A	B117RSW	B117RSW	N/A	N/A
9368-E	N/A	N/A	N/A	N/A	N/A	N/A
9368-EK	N/A	N/A	N/A	N/A	N/A	N/A
9368-EW	6070-4/E214	N/A	B120R	BH118R	EZ21S0	S118W
9368-EWK	6070-4/E214	N/A	B120R	BH118R	EZ21S0	S118W
9372-NMHK	N/A	N/A	N/A	N/A	N/A	N/A
RD-42	RD-30	N/A	B234ADJC/RDS-30	N/A	N/A	P242RRD
RD-42SS	N/A	N/A	N/A	N/A	N/A	P242SRD

fiberglassBOX™: Paddle Fan Support Boxes

Allied Moulded	Westinghouse	Arlington	Raco	Carlton PC	Steel City (T&B)	Carlton PH	Reiker (P&S)	Slater (P&S)
9335-NFR/NKFR	N/A	FB417S/FBS420S	N/A	N/A	N/A	N/A	N/A	N/A
9336-NKFR	01040-11	FBS415S	N/A	N/A	N/A	N/A	N/A	N/A
9350-FAN/FANB	N/A	N/A	927/928	N/A	N/A	4070-CFB-BHL	65521/85502	N/A
9350-FRBKOW	N/A	FBRS420R	934	N/A	N/A	N/A	22200	N/A
9350-KFR	N/A	FB423/FBS420	7120/299	B720-SHK	54171-CFB	CFB-16	44400/55528	S1-6-FAN
9351-NFR/NKFR	01240-11	FB417S	294-1	BH525L/BH525LP	54171-F-CFB	4170-CFB	55020/55025	S1-20-RFAN
9364-FAN/FANB	01525/ 01100/ 01010	N/A	925/926	MB715H	N/A	N/A	N/A	N/A
9364-FRBKOW	N/A	N/A	935	MB715RH	54151CFB-BHL-OW	N/A	33310/83300	N/A
9364-KFR	01050-11	FBS426	N/A	N/A	N/A	N/A	33303/55505	N/A
9365-NKFR	01250-11	N/A	N/A	BH525L	N/A	N/A	55015/33303	N/A
9369-FB	01020-11	FBS426	296-1	MB715S	54151-CFB	N/A	N/A	N/A
9369-FBH	01250	FBS415S	N/A	N/A	N/A	N/A	N/A	N/A
9369-FRBKB	0152511	FBRS415	926-1	MB715H	54151CFB-BHL	N/A	55501	N/A
9370-FR	01030	FB407	N/A	N/A	N/A	N/A	N/A	S1-09-FAN
9373-FR	02000	FB443	7120	CFB-16	N/A	N/A	N/A	S1-16-FAN
9375-FR	02525	FB442/FB412	7120	CFB-12	N/A	N/A	N/A	N/A