



A10106CH 10X10X6 N12 CH W/CLMPS

Hoffman Enclosures, Inc.

Catalog Number	A10106CH
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure Clamps CH Type 12, 10X10X6, Gray, Mild Steel
Weight per unit	48.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP65
Material	Mild Steel;Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Size	10.00x10.00x6.00 in
Width	10

Descriptions

Description	10X10X6 N12 CH W/CLMPS
extra long description	NVENT HOF A10106CH CH Box 10.00x10.
Features	This easy-to-open, continuous hinge enclosure features screw-down clamps for secure closure and can be used in a wide variety of applications.
Long Description	Continuous Hinge Enclosure Clamps CH Type 12, 10x10x6, Gray, Mild Steel
Product Type	CH Box 10.00X10.00X6.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510548803
Manufacturers Part Number	A10106CH
UPC	783510548803

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Terminal and Junction Boxes

Packaging

Carton	1
Package	4
Weight Per each	48



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82
76240-0000, TX Gainesville
Phone: 940-612-1388
Fax: 940-612-1499

Uses, Certifications, and Standards

Application

Controls and Drives

nema rating

12