



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A1412CHNFSS 14X12X6 N4X CH, CLMP LTCH

Hoffman Enclosures, Inc.

Catalog Number	A1412CHNFSS
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge With Clamps Junction Box Type 4X, 14X12X6, Brushed, Stainless 304
Weight per unit	30.1 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Size	14.00x12.00x6.00 in
Width	12

Descriptions

Description	14X12X6 N4X CH,CLMP LTCH
extra long description	NVENT HOF A1412CHNFSS Stainless CHN
Features	Used in either indoor or outdoor applications, these enclosures combine a rugged continuous hinge, seamless foam-in-place gasket and stainless steel screw-down clamps for a reliable seal that protects components from corrosive environments.
Long Description	Continuous Hinge with Clamps Junction Box Type 4X, 14x12x6, Brushed, Stainless 304
Product Type	Stainless CHNFSS Box 14.00
Short Description	Stainless CHNFSS Box 14.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510563004
Manufacturers Part Number	A1412CHNFSS
UPC	783510563004

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Terminal and Junction Boxes



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	2
Weight Per each	30.08

Uses, Certifications, and Standards

Application	Controls and Drives;Corrosive Environments
nema rating	4X