



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street  
72758-6430, AR Rogers  
Phone: 479-636-4190  
Fax: 479-636-5604



## **A181610PHC 18.6X16.6X10.1 N4X SLD HC**

*Hoffman Enclosures, Inc.*

Catalog Number	A181610PHC
Manufacturer	Hoffman Enclosures, Inc.
Description	Polypro Type 4X, 17.95X15.94X10.35, Polyester
Weight per unit	13.0 (lbs/each)
Product Category	Nema Type 1 Metallic Enclosure

### **Features**

ip rating	IP66
Material	Polyester

### **Material, Color, and Finish**

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte

### **Dimensions and Weight**

Height	18.58
Size	17.95x15.94x10.35 in
Width	16.58

### **Descriptions**

Description	18.6X16.6X10.1 N4X SLD HC
extra long description	NVENT HOF A181610PHC TYPE 4X POLY S
Features	PolyPro polyester enclosures perform exceptionally well in applications where harsh chemicals, weather extremes and corrosive environments demand toughness from a lightweight enclosure. Providing excellent ultraviolet protection and a tight environmental seal, these versatile, feature-rich enclosures are also recyclable.
Long Description	PolyPro Type 4X, 17.95x15.94x10.35, Polyester
Product Type	Type 4X Poly Solid CVR QR/SC

### **Manufacturer Information**

Brand	Nvent Hoffman
GTIN	00783510170813
Manufacturers Part Number	A181610PHC
UPC	783510170813

### **Taxonomies, Classifications, and Categories**

Category Description	PVC BOXES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street  
72758-6430, AR Rogers  
Phone: 479-636-4190  
Fax: 479-636-5604

## Packaging

Carton	1
Weight Per each	13

## Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X