



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A242408LP 24X24X8 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A242408LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wall-Mount Enclosure, Steel, Type 12 Continuous Hinge, Wall Mount, White (Inside);Ansi 61 Gray (Outside), White (Inside);Gray (Door), 24 In Overall Width, 24 In Overall Length, 8 In Overall Height, 43 LB
Weight per unit	43.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	8
Height	24
Size	24.00x24.00x8.00 in
Width	24

Descriptions

Description	24X24X8 N12 CH CLMP CVR
extra long description	NVENT HOF A242408LP Enclosure 24.00
Features	For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510282103
UPC	783510282103

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	43

Uses, Certifications, and Standards

nema rating	12 Indoor, dust-resistant
-------------	---------------------------