



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A242410LP 24X24X10 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

| | |
|------------------|---|
| Catalog Number | A242410LP |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Continuous Hinge Enclosure With Clamps LP Type 12, 24X24X10, Gray, Mild Steel |
| Weight per unit | 53.0 (lbs/each) |
| Product Category | Nema Types 12 & 13 Metallic En |

Features

| | |
|-----------|------------|
| ip rating | IP65 |
| Material | MILD STEEL |

Material, Color, and Finish

| | |
|--------|---------------|
| Finish | Powder Coated |
|--------|---------------|

Dimensions and Weight

| | |
|--------|----------------------|
| Depth | 10 |
| Height | 24 |
| Size | 24.00x24.00x10.00 in |
| Width | 24 |

Descriptions

| | |
|------------------------|--|
| Description | 24X24X10 N12 CH CLMP CVR |
| extra long description | NVENT HOF A242410LP Enclosure 24.00 |
| Features | For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure. |
| Long Description | Continuous Hinge Enclosure with Clamps LP Type 12, 24x24x10, Gray, Mild Steel |
| Product Type | Enclosure 24.00X24.00X10.00 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510284008 |
| Manufacturers Part Number | A242410LP |
| UPC | 783510284008 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STEEL JUNCTION BOXES |
| Type | Mild Steel Wall Mounted Industrial Enclosures |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 53 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Controls and Drives

nema rating

12 Indoor, dust-resistant