



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Single Row Terminal Block

A31931007MP

UPC:051712345323

### Dimensions:

- **Height:** .001 IN
- **Length:** 3.5 IN
- **Width:** .65 IN

**Weight:**.1 LB

### Warranties:

- Not Applicable

### Specifications:

- **Application:** industrial
- **Mounting:** insulator base/mount end
- **Special Features:** Break down voltage 3500V
- **Type:** Standard barrier
- **Voltage Rating:** 600V
- **Number Of Poles:** Ten-pole
- **Operating Temperature:** -40° to 105°C
- **Wire Size:** #22 to 12 AWG (Copper)
- **Torque Rating:** 9 lb-in
- **Center Spacing:** 0.437 in
- **Screw Options:** Steel SEMS zinc-plated screw
- **Material:** Molded thermoplastic base, zinc plated steel screw
- **Color:** Black
- **Connection:** #6-32 TPI screw, hand wired
- **Terminal Material:** 0.250" QC short

**Supporting documents:** No Data

**Certifications:** No Data

### Product compliance:

- CE Marked



