

# Security/Fire Alarm Cable (CMR) Unshielded

Solid Bare Copper  
Flame Retardant PVC Insulation  
105°C , 300 Volt



## APPLICATIONS

Southwire's Security/Fire Alarm Cable(CMR) Unshielded is suitable for interconnection of electrical devices within a security & fire protective signaling system. For use in dry or damp locations.

## SPECIFICATIONS

Southwire's Security/Fire Alarm Cable(CMR) Unshielded meets the following applicable requirements:

- CSA Spec. C22.2, No. 208
- File Listing: LL68731
- UL Listed as Type CMR or FPLR 75°C, FT-4
- Available in Colors: Black, Red, Brown, Blue

## CONSTRUCTION

Southwire's Security/Fire Alarm Cable(CMR) Unshielded is constructed with solid bare copper, polyvinylchloride insulation and an overall polyvinylchloride jacket for data communications/security applications manufactured in the USA and UL listed FPLR 75°C, FT-4.

# Security/Fire Alarm Cable (CMR) Unshielded

Size (AWG)	No. Of. Conds.	Nominal Insulation Thickness (in)	Nominal Jacket Thickness (in)	Nominal Overall Diameter (in)	Weight (lbs/1000ft)
UNSHIELDED					
18	2	0.0007	0.015	0.140	17
18	4	0.0007	0.015	0.162	29

# Security/Fire Alarm Cable (CMR) Unshielded

Solid Bare Copper  
Flame Retardant PVC Insulation  
105°C , 300 Volt



## APPLICATIONS

Southwire's Security/Fire Alarm Cable(CMR) Unshielded is suitable for interconnection of electrical devices within a security & fire protective signaling system. For use in dry or damp locations.

## SPECIFICATIONS

Southwire's Security/Fire Alarm Cable(CMR) Unshielded meets the following applicable requirements:

- CSA Spec. C22.2, No. 208
- File Listing: LL68731
- UL Listed as Type CMR or FPLR 75°C, FT-4
- Available in Colors: Black, Red, Brown, Blue

## CONSTRUCTION

Southwire's Security/Fire Alarm Cable(CMR) Unshielded is constructed with solid bare copper, polyvinylchloride insulation and an overall polyvinylchloride jacket for data communications/security applications manufactured in the USA and UL listed FPLR 75°C, FT-4.

# Security/Fire Alarm Cable (CMR) Unshielded

Size (AWG)	No. Of. Conds.	Nominal Insulation Thickness (in)	Nominal Jacket Thickness (in)	Nominal Overall Diameter (in)	Weight (lbs/1000ft)
UNSHIELDED					
18	2	0.0007	0.015	0.140	17
18	4	0.0007	0.015	0.162	29



**Southwire**  
One Southwire Drive  
Carrollton, Ga. 30119 USA



**greenSpec**  
RoHS Compliant

Copyright 2010, Southwire Company.  
All Rights Reserved.

®Southwire is a registered trademark  
of Southwire Company.