



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AF205301113 CTR, 3P, 192A, 100-250VAC/DC Contactors

*Industrial Connections &*

|                  |  |
|------------------|--|
| Catalog Number   | AF205301113  |
| Manufacturer     | Industrial Connections &   |
| Description      | 3 Pole, 300 Amp Across The Line Contactor With 100-250V Ac Coil and 1 No and 1 NC Auxiliary Contacts |
| Weight per unit  | 7,160.0 (lbs/each)   |
| Product Category | IEC Contactors   |

### Dimensions and Weight

|      |               |
|------|---------------|
| Size | 105x196x152mm |
|------|---------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | CTR,3P,192A,100-250VAC/DC CONTACTORS   |
| extra long description | ABB AF205-30-11-13 CTR,3P,192A,100-  |
| Long Description       | 3 pole, 300 amp across the line contactor with 100-250V AC coil and 1 NO and 1 NC auxiliary contacts |
| Product Type           | CTR, 3P, 192A, 100-250VAC/DC, 1/1  |
| Special Features       | Terminal type: Screw terminals   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | ABB            |
| GTIN                      | 00888614148017 |
| Manufacturers Part Number | AF205-30-11-13 |
| UPC                       | 888614148017   |

### Taxonomies, Classifications, and Categories

|                      |                   |
|----------------------|-------------------|
| Category Description | FREEDOM/IEC STYLE |
| Type                 | Contactors        |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 7160 |

### Uses, Certifications, and Standards

|                       |                      |
|-----------------------|----------------------|
| Operating Temperature | -25 to +50 Degrees C |
| standard              | CB, CE, RINA, RoHS   |