



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AF265301113 3P 248A CNCTR

Industrial Connections &

Catalog Number	AF265301113
Manufacturer	Industrial Connections &
Description	A 3-Phase Contactor Suitable For Various Applications Such As Motor Starting, Isolation, By-Pass and Distribution Application Up to Max 1000 V. Operated With Wide Control Voltage Range 100-250 V, 50/60 HZ and DC
Weight per unit	11.9 (lbs/each)
Product Category	IEC Contactors

Dimensions and Weight

Size	140x225x180mm
------	---------------

Descriptions

Description	3P 248A CNCTR
extra long description	ABB AF265-30-11-13 CTR,3P,248A,100-
Long Description	A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, By-pass and Distribution application up to max 1000 V. Operated with wide control voltage range 100-250 V, 50/60 Hz and DC
Product Type	Contacteur 3 Pole 250HP 600vca
Special Features	Terminal type: Screw terminals

Manufacturer Information

Brand	ABB
GTIN	00888614142695
Manufacturers Part Number	AF265-30-11-13
UPC	888614142695

Taxonomies, Classifications, and Categories

Category Description	IEC/FREEDOM CONTACTOR
Type	Contactors

Packaging

Carton	1
Weight Per each	11.87

Uses, Certifications, and Standards

Application	Suitable for various applications such as motor starting, isolation, by-pass and distribution application up to max 690 V.
Operating Temperature standard	-25 to +50 Degrees C CB, CE, RINA, RoHS