

Specifications



Eaton AGC-7-R

Eaton ABC series Fast-acting fuse, 1A, 250 Vac, 125 Vdc, 32 Vac (self certified)

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Bussmann series AGC fast-acting glass tube fuse |
| CATALOG NUMBER | AGC-7-R |
| UPC | 051712655279 |
| PRODUCT LENGTH/DEPTH | 1.25 in |
| PRODUCT HEIGHT | 0.25 in |
| PRODUCT WIDTH | 0.25 in |
| PRODUCT WEIGHT | 0.004 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | RoHS Compliant CE Marked |

Product specifications

| | |
|------------------|--|
| USED WITH | out axial leads |
| AMPERAGE RATING | 7 A |
| INTERRUPT RATING | 10 kAIC at 125 Vac 200 AIC at 250 Vac |
| FUSE INDICATOR | Non-indicating |
| CONNECTION | Ferrule end x ferrule end |
| RESPONSE TIME | 60 min at 135%, 120 sec at 200% |
| MATERIAL | Glass tube Nickel-plated brass end cap construction |
| QUANTITY | 5 |
| VOLTAGE RATING | 250 Vac, 32 Vdc (self certified) |
| TYPE | Electronic |
| APPLICATION | Electronic circuits |

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton AGC fast-acting glass tube fuses data-sheet](#)

[Eaton Specification Sheet - AGC-7-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

