



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH430R12W Recept Pin&Sleeve 30A 125/250V 3P4W WT or *Eaton Wiring Devices*

Catalog Number	AH430R12W
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Pin and Sleeve Receptacle, IP69K Rated, #10 -#2 Awg, 30A, Extra Heavy-Duty, 125/250V, Back Wire, Orange, Nickel Plated Brass, IP67, IP69K, Nylon, Three-Pole, Four-Wire, Grounding, AHBB30 Back Box Style, Female, Nylon
Weight per unit	32.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Pin & Sleeve
dimensions	3.7500 IN X 4.2100 IN X 3.1250 IN
insulation	Nylon PA6-GF30FR (17)
Material	Nylon;Other
media	Yes
Phase	3
Poles	3
Voltage Rating	125/250V/AC

Material, Color, and Finish

Color	Blue & Gray
-------	-------------

Dimensions and Weight

Size	5.5 x 4.75 x 5
------	----------------

Descriptions

Description	RECP PIN&SLEEVE 30A 125/250V 3P4W WT OR
extra long description	EWD AH430R12W Recept Pin&Sleeve 30A 1
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	Eaton Arrow Hart pin and sleeve receptacle, IP69K Rated, #10 -#2 AWG, 30A, Extra Heavy-Duty, 125/250V, Back wire, Orange, Nickel plated brass, IP67, IP69K, Nylon, Three-pole, Four-wire, grounding, AHBB30 Back box style, Female, Nylon
Product Type	Recept Pin&Sleeve 30A 125/250V 3P4W WT or
Special Features	Watertight P&S receptacles



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00326647319528
Manufacturers Part Number	AH430R12W
UPC	032664731952

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Pin and Sleeve receptacle

Packaging

Carton	1
Package	32
Weight Per each	32

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	IP67 & IP69k
Mounting	Flange Mount
standard	cRUus
Temperature Rating	Max. 30°C (86°F) after 50 cycles of overload @150% of rated current