



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AHIGL630R Recp Single Ig 30A 250V 2P3W H/L or *Eaton Wiring Devices*

| | |
|------------------|---|
| Catalog Number | AHIGL630R |
| Manufacturer | Eaton Wiring Devices |
| Description | Eaton Locking Receptacle, #14-8 Awg, 30A, Industrial, 250V, Back and Side Wiring, Orange, Single, L6-30, Two-Pole, Three-Wire, Glass-Filled Nylon |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------|-----------------------------------|
| dimensions | 4.2500 IN X 2.0000 IN X 1.7500 IN |
| media | Yes |

Descriptions

| | |
|------------------------|---|
| Description | RECP SINGLE IG 30A 250V 2P3W H/L OR |
| extra long description | EWD AHIGL630R Recp Single IG 30A 25 |
| Features | Industrial grade locking devices are designed for quick and easy installation and provide reliable performance in tough industrial environments. |
| Long Description | Eaton locking receptacle, #14-8 AWG, 30A, Industrial, 250V, Back and side wiring, Orange, Single, L6-30, Two-pole, Three-wire, Glass-filled nylon |
| Product Type | Recp Single Ig 30A 250V 2P3W H/L or |
| Special Features | Industrial grd recepts |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Arrow Hart |
| GTIN | 00040893677187 |
| Manufacturers Part Number | IGL630R |
| UPC | 040893677187 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | Industrial cord connectors |
| Type | Locking isolated ground receptacle |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.3 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Ind Facilities & Factories - Facility - Other |
| standard | UL,Federal Specification Classification 6233 01,NOM,CSA certified,RoHS Compliant |