

**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

AMS4/0  
 7818102410288  
 4/0-6 DUAL RATED SPLICE  
 Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Width (in)	1.00
Length (in)	2.31
Hex Size	5/16
H1	1.09
General	
Number of Screws	2
Product Description	Aluminum Mechanical Splice, 4/0-6 AWG, 9/16" Screw Dia, 2 Screws, 5/16" Hex Size, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 AWG-4/0 AWG
Copper Solid Size (Range)	6 AWG-4/0 AWG
Copper Stranded (Range)	6 AWG-4/0 AWG
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Splice, Reducer
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us


**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

AMS4/0  
 7818102410288  
 4/0-6 DUAL RATED SPLICE  
 Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Width (in)	1.00
Length (in)	2.31
Hex Size	5/16
H1	1.09
General	
Number of Screws	2
Product Description	Aluminum Mechanical Splice, 4/0-6 AWG, 9/16" Screw Dia, 2 Screws, 5/16" Hex Size, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 AWG-4/0 AWG
Copper Solid Size (Range)	6 AWG-4/0 AWG
Copper Stranded (Range)	6 AWG-4/0 AWG
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Splice, Reducer
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175