



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AYP040 4/0 Al/Cu Offset Comp Terminal

Burndy LLC

Catalog Number	AYP040
Manufacturer	Burndy LLC
Description	Aluminum Compression Pin Adapter, 4/0 Awg, 0.42" Plug Dia, 1.22" Plug Length, Al/Cu Rated, Tin Plated.
Weight per unit	0.1200 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Conductor Type	CODE/FLEX
Die Index	298
insulation	Y
Insulation Type	Rubber
Material	Aluminum
pallet quantity	2960
Voltage Rating	35

### Material, Color, and Finish

Color Code	WHITE
Finish	Tin-Plated

### Descriptions

Description	4/0 AL/CU OFFSET COMP TERMINAL
extra long description	BUR AYPO4/0 4/0STR AL OFFSET HYPLUG
Long Description	Aluminum Compression Pin Adapter, 4/0 AWG, 0.42" Plug Dia, 1.22" Plug Length, Al/Cu Rated, Tin Plated.
Product Type	Terminal
Special Features	Features: All-Aluminum Electro-Tin Plated design eliminates possible bi-metallic corrosion and provides shortest connector length design possible for easy installation in equipment with limited space. Solid electro-tin plated aluminum plug makes properly connection easily. Smooth surface on the solic EC plug provides greater area contact establishing excellent conductivity. Solid plug has equivalent cross-sectional area as current carrying equivalent copper wire permitting use of larger aluminum wire to co

### Manufacturer Information

Brand	BURNDY
GTIN	00781810738368
Manufacturers Part Number	AYPO4/0
UPC	781810738368



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Aluminum Pin Adapters

## Packaging

Carton	1
Package	10
Weight Per each	0.12

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B
Temperature Rating	194