



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



B22SHAGALV10 BLTD 1-5/8X3-1/4X120 12GA GLV BK2BK SLTD, 2" CNTR *Cooper B-Line/Cable Tray*

Catalog Number	B22SHAGALV10
Manufacturer	Cooper B-Line/Cable Tray
Description	SH Type Channel, Low Carbon Steel, Pre Galvanized, 10 FT Length, 1-5/8 In Height, 12 Awg Thickness, 2 In Center Spacing, 9/16 X 1-1/8 In Slot Size, 1.82 LB/FT
Weight per unit	3.6 (lbs/each)
Product Category	Channel & Strut

Features

dimensions	120.0000 IN X 1.6200 IN X 1.6200 IN
gauge	12

Material, Color, and Finish

material composition	Cold Formed Low Carbon Steel
material standard	ASTM A653

Dimensions and Weight

Depth	3-1/4 In
Width	1-5/8 in

Descriptions

Also Known As...	Strut
	Strut channel
Description	BLTD 1-5/8X3-1/4X120 12GA GLV BK2BK SLTD, 2" CNTR
extra long description	B-LINE B22SHA-120GLV CHNL, 1 5/8" X
Features	Eaton offers a wide range of back to back and welded configured strut combinations for a variety of support applications.
similar brands	Unistrut
Special Features	2 In Center Spacing

Manufacturer Information

Brand	Eaton
GTIN	00781011034450
UPC	781011034450

Taxonomies, Classifications, and Categories

Category Description	STRUT CHANNEL
Type	Strut back-to-back welded channel

Availability

minimum qty	10
Status	Inactive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per foot	3.64

Uses, Certifications, and Standards

standard	Not Applicable
----------	----------------