

Specifications



Eaton BBS-15

Eaton Bussmann series BBS fuse, 15 A, Non-indicating, Ferrule end x ferrule end, Consult factory, Nickel-plated brass endcaps, Standard, 48 V

General specifications

| | |
|-----------------------------|--------------------------------|
| PRODUCT NAME | Eaton Bussmann series BBS fuse |
| CATALOG NUMBER | BBS-15 |
| UPC | 051712707527 |
| EAN | 5027590056915 |
| PRODUCT LENGTH/DEPTH | 0.41 in |
| PRODUCT HEIGHT | 1.38 in |
| PRODUCT WIDTH | 0.41 in |
| PRODUCT WEIGHT | 0.12 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | CE Marked |



Powering Business Worldwide

Electrical rating

AMPERAGE RATING 15 A

INTERRUPT RATING Consult factory

VOLTAGE RATING 48 V

General information

CONNECTION Ferrule end x ferrule end

FUSE INDICATOR Non-indicating

SPECIAL FEATURES Silver-plated fuse caps

Physical details

MATERIAL Nickel-plated brass endcaps

PACKAGING TYPE Standard

Resources

CATALOGS [Bussmann series complete full line catalog no. 1007](#)

MULTIMEDIA [Bussmann series Fuseology](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - BBS-15](#)

TECHNICAL DATA SHEETS [BBS-15~BUSS MIDGET FUSE FAST ACTING](#)

TECHNICAL SERVICE BULLETINS [Datasheet - FNQ-30](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

