



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BGRB B-Cap Wire Connector, BGR Green Grounding, 250/Box**

*Ideal*

Catalog Number	BGRB
Manufacturer	Ideal
Description	Wire Connector, (2) #14 Awg Conductor Size, (5) #12 Awg Conductor Size, Green Insulation Color, +221 °F Operating Temperature, 2 to 5 Conductors, 0.01 LB
Weight per unit	0.0070 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### **Features**

Material	Flame-retardant Polypropelene
----------	-------------------------------

### **Material, Color, and Finish**

Color	Green
-------	-------

### **Descriptions**

Description	B-CAP WIRE CONNECTOR,BGR GREEN GROUNDING, 250/BOX
extra long description	IDEAL BGR-B BGR GREEN GROUND, 250 B
Features	The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you're retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de

### **Manufacturer Information**

Brand	Buchanan
GTIN	00781789453675
UPC	781789453675

### **Taxonomies, Classifications, and Categories**

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

### **Availability**

minimum qty	250
Status	Inactive

### **Packaging**

Carton	250
Weight Per each	0.007



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

environmental conditions

Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)

standard

CSA C22.2 #188, UL 467 Listed, RoHS