

# Specifications



Photo is representative

## Eaton BKED225

Eaton Pow-R-stock series Main circuit breaker kit, ED circuit bkr type, Top and Bottom Mounting, Single- or three-phase, 225A

### General specifications

PRODUCT NAME	Eaton Pow-R-Stock main breaker kit
CATALOG NUMBER	BKED225
UPC	786689030858
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	4.13 in
PRODUCT WEIGHT	5 lb
CERTIFICATIONS	UL Listed
GLOBAL CATALOG	BKED225

## Product specifications

CIRCUIT BREAKER TYPE	ED
MOUNTING	Top, bottom
PHASE	Single-phase, three-phase
RATED OPERATIONAL CURRENT	225A
SERIES	Pow-R-stock

## Resources

MULTIMEDIA	<a href="#">Pow-R-Line Xpert family overview</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BKED225</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative

## Eaton BKED225

Eaton Pow-R-stock series Main circuit breaker kit, ED circuit bkr type, Top and Bottom Mounting, Single- or three-phase, 225A

### General specifications

PRODUCT NAME	Eaton Pow-R-Stock main breaker kit
CATALOG NUMBER	BKED225
UPC	786689030858
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	4.13 in
PRODUCT WEIGHT	5 lb
CERTIFICATIONS	UL Listed
GLOBAL CATALOG	BKED225

## Product specifications

CIRCUIT BREAKER TYPE	ED
MOUNTING	Top, bottom
PHASE	Single-phase, three-phase
RATED OPERATIONAL CURRENT	225A
SERIES	Pow-R-stock

## Resources

MULTIMEDIA	<a href="#">Pow-R-Line Xpert family overview</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BKED225</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

