

Specifications



Eaton BR1224B100R

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 100A, single-phase, 24-pole, 24 circuits, 12 spaces, 120/240V, #4-1/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 3R enclosure, b2r box size

General specifications

| | |
|-----------------------------|----------------------------------|
| PRODUCT NAME | Eaton BR main breaker loadcenter |
| CATALOG NUMBER | BR1224B100R |
| UPC | 786676443951 |
| PRODUCT LENGTH/DEPTH | 20.4 in |
| PRODUCT HEIGHT | 5.5 in |
| PRODUCT WIDTH | 15.1 in |
| PRODUCT WEIGHT | 22.6 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 67 UL 50 |

Product specifications

| | |
|-----------------------------|-------------------------|
| SPECIAL FEATURES | No feed-thru lugs |
| TYPE | Main circuit breaker |
| AMPERAGE RATING | 100 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BR |
| NUMBER OF CIRCUITS | 24 |
| NUMBER OF SPACES | 12 |
| PHASE | Single-phase |
| WIRE SIZE | #4-1/0 AWG Cu/Al |
| USED WITH | Type BR 1-inch breakers |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | B2R |
| ENCLOSURE | NEMA 3R |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 10 kAIC |
| NUMBER OF WIRES | 3 |



Specifications



Eaton BR1224B100R

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 100A, single-phase, 24-pole, 24 circuits, 12 spaces, 120/240V, #4-1/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 3R enclosure, b2r box size

General specifications

| | |
|-----------------------------|----------------------------------|
| PRODUCT NAME | Eaton BR main breaker loadcenter |
| CATALOG NUMBER | BR1224B100R |
| UPC | 786676443951 |
| PRODUCT LENGTH/DEPTH | 20.4 in |
| PRODUCT HEIGHT | 5.5 in |
| PRODUCT WIDTH | 15.1 in |
| PRODUCT WEIGHT | 22.6 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 67 UL 50 |

Product specifications

| | |
|-----------------------------|-------------------------|
| SPECIAL FEATURES | No feed-thru lugs |
| TYPE | Main circuit breaker |
| AMPERAGE RATING | 100 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BR |
| NUMBER OF CIRCUITS | 24 |
| NUMBER OF SPACES | 12 |
| PHASE | Single-phase |
| WIRE SIZE | #4-1/0 AWG Cu/Al |
| USED WITH | Type BR 1-inch breakers |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | B2R |
| ENCLOSURE | NEMA 3R |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 10 kAIC |
| NUMBER OF WIRES | 3 |

