

Specifications



Eaton BR1224N200R

Eaton BR convertible loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, Convertible main, 200 A, C3r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 24 Circuits, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BR1224N200R
UPC	786676448550
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	27 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	The maximum rating of the panel is the main breaker rating when used as service entrance equipment. Has notch for brhdk125 hold-down kit.

Product specifications

SPECIAL FEATURES	No feed-thru lugs, includes BREQS125 hold-down screw
TYPE	Convertible main
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	12
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
WIRE SIZE	Determined by circuit breaker installed
BOX SIZE	C3R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS

[Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BR1224N200R](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton BR1224N200R

Eaton BR convertible loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, Convertible main, 200 A, C3r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 24 Circuits, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BR1224N200R
UPC	786676448550
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	27 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	The maximum rating of the panel is the main breaker rating when used as service entrance equipment. Has notch for brhdk125 hold-down kit.

Product specifications

SPECIAL FEATURES	No feed-thru lugs, includes BREQS125 hold-down screw
TYPE	Convertible main
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	12
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
WIRE SIZE	Determined by circuit breaker installed
BOX SIZE	C3R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS

[Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BR1224N200R](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

