



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR1624L125

UPC:786676446754

Dimensions:

- **Height:** 18.75 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Notes:Has notch for brhdk125 hold-down kit.

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs, includes BREQS125 hold-down screw
- **Type:** Main lug
- **Amperage Rating:** 125A
- **Box Size:** B2
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Mounting:** Combination
- **Number Of Circuits:** 24
- **Number Of Spaces:** 16
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #6-2/0 AWG Cu/Al

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR1624L125](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR1624L125

UPC:786676446754

Dimensions:

- **Height:** 18.75 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Notes:Has notch for brhdk125 hold-down kit.

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs, includes BREQS125 hold-down screw
- **Type:** Main lug
- **Amperage Rating:** 125A
- **Box Size:** B2
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Mounting:** Combination
- **Number Of Circuits:** 24
- **Number Of Spaces:** 16
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #6-2/0 AWG Cu/Al

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR1624L125](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.