



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR2024B125 20/24C 125A 1PH MB Loadcenter

Eaton Corp

Catalog Number	BR2024B125
Manufacturer	Eaton Corp
Description	BR Style Load Center, 20 Spaces, 24 Circuits, 125 A, 120/240 V Ac, #4 to 2/0 Awg Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 21 In Overall Height
Weight per unit	24.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	125
Cover Type	Cover included
max amps	125
max spaces/poles	20/24
Phase	1

Dimensions and Weight

Depth	3.88
Height	16.75
Size	C1
Width	14.31

Descriptions

Description	20/24C 125A 1PH MB LOADCENTER
extra long description	ETN BR2024B125 Eaton BR main breake

Manufacturer Information

GTIN	00786676444453
UPC	786676444453

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	24

Uses, Certifications, and Standards

Mounting	Combination Mount
standard	UL 67,UL 50