

Eaton BR3040B200R

Catalog Number: BR3040B200R

Value pack, Main circuit breaker loadcenter, 200A, C3, Aluminum, Interlock cover, NEMA 3R, Metallic, 10 kAIC, BR, 40 circuits, Forty pole, 30 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR3040B200R
UPC	Product Length/Depth
786676446051	5.19 in
Product Height	Product Width
25 in	14.31 in
Product Weight	Warranty
43 lb	10 year

Certifications

UL 67
UL 50

Product specifications

Special features

Value pack

Type

Main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Interlock cover

Main circuit breaker

BR

Number of circuits

40

Number of spaces

30

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

C3

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR3040B200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)