

# Eaton BR3040B200RV

Catalog Number: BR3040B200RV

No feed-thru lugs, Main circuit breaker loadcenter, 200A, D1R, Aluminum, Interlock cover, NEMA 3R, Metallic, 25 kAIC, BWH, 40 circuits, Forty pole, 30 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BR3040B200RV
<b>UPC</b>	<b>Product Length/Depth</b>
786676002226	5.19 in
<b>Product Height</b>	<b>Product Width</b>
29.13 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
40.62 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Includes 5-br120 & 1 br230

## Product specifications

### Special features

No feed-thru lugs

### Type

Main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Interlock cover

### Main circuit breaker

BWH

### Number of circuits

40

### Number of spaces

30

### Phase

Single-phase

### Wire size

#2/0 AWG-300 kcmil Cu/Al

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

D1R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BR3040B200RV](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)