

Specifications

Eaton BR3040L200R

Eaton BR main lug loadcenter, No feed-thru lugs, 200 A, D1R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 40 Circuits, Twenty-four pole, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1 AWG-300 kcmil Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR3040L200R
UPC	786676447706
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	29.13 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	43 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Has notch for brhdk125 hold-down kit.

Product specifications

SPECIAL FEATURES	No feed-thru lugs
TYPE	Main lug
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	30
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	D1R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR3040L200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

