



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton BR style 1-inch loadcenter

**BR3040N200G**

**UPC:**782116893928

### Dimensions:

- **Height:** 29.13 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

**Weight:**34 LB

### Warranties:

- 10 year

### Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** D1r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 40
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** Determined by circuit breaker installed

### Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR3040N200G](#)

**Certifications:**

- UL 67
- UL 50

**Product compliance:** No Data



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton BR style 1-inch loadcenter

**BR3040N200G**

**UPC:**782116893928

### Dimensions:

- **Height:** 29.13 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

**Weight:**34 LB

### Warranties:

- 10 year

### Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** D1r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 40
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** Determined by circuit breaker installed

### Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR3040N200G](#)

**Certifications:**

- UL 67
- UL 50

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.