

# Specifications

## Eaton BR3060BQN150

BR loadcenter, 150A CSR MAIN BREAKER, 30 SPACES/60 CIRCUITS, 120/240V, ALUMINUM BUS, G1 INDOOR BOX SIZE, #2-300MCM INCOMING LUG SIZE, QUICK CONNECT NEUTRAL CONFIGURATION



### General specifications

<b>PRODUCT NAME</b>	Eaton BR main breaker loadcenter
<b>CATALOG NUMBER</b>	BR3060BQN150
<b>UPC</b>	786676026277
<b>PRODUCT LENGTH/DEPTH</b>	3.88 in
<b>PRODUCT HEIGHT</b>	34.13 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	34 lb
<b>WARRANTY</b>	10 year



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	QUICK CONNECT NEUTRALS
<b>TYPE</b>	Main circuit breaker
<b>AMPERAGE RATING</b>	150 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	CSR
<b>NUMBER OF CIRCUITS</b>	60
<b>NUMBER OF SPACES</b>	30
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#2 AWG-300 kcmil
<b>MOUNTING</b>	Combination
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240 V
<b>BOX SIZE</b>	G1
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	25 kAIC
<b>NUMBER OF WIRES</b>	3

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BR3060BQN150](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton BR3060BQN150

BR loadcenter, 150A CSR MAIN BREAKER, 30 SPACES/60 CIRCUITS, 120/240V, ALUMINUM BUS, G1 INDOOR BOX SIZE, #2-300MCM INCOMING LUG SIZE, QUICK CONNECT NEUTRAL CONFIGURATION



### General specifications

<b>PRODUCT NAME</b>	Eaton BR main breaker loadcenter
<b>CATALOG NUMBER</b>	BR3060BQN150
<b>UPC</b>	786676026277
<b>PRODUCT LENGTH/DEPTH</b>	3.88 in
<b>PRODUCT HEIGHT</b>	34.13 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	34 lb
<b>WARRANTY</b>	10 year



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	QUICK CONNECT NEUTRALS
<b>TYPE</b>	Main circuit breaker
<b>AMPERAGE RATING</b>	150 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	CSR
<b>NUMBER OF CIRCUITS</b>	60
<b>NUMBER OF SPACES</b>	30
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#2 AWG-300 kcmil
<b>MOUNTING</b>	Combination
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240 V
<b>BOX SIZE</b>	G1
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	25 kAIC
<b>NUMBER OF WIRES</b>	3

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - BR3060BQN150</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

